

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [5054331081](#)
Status: **Active**
Overview: Micro-Lock Plus Connector System
Description: 1.25mm Pitch, Micro-Lock Plus PCB Header, Dual Row, Vertical, Surface Mount, Tin-Bismuth Plating, Positive Lock, 10 Circuits, with Pick-and-Place Polyimide Tape, Black

Documents:

3D Model (PDF)	Product Specification 5054321000-PS-006 (PDF)
3D Model	Application Specification 5054320000-AS-000 (PDF)
Drawing (PDF)	Application Specification AS-505432-001-001 (PDF)
Product Specification 2145270000-PS-000 (PDF)	Packaging Specification 5054339200-200 (PDF)
Product Specification 5054320000-002 (PDF)	Datasheet (PDF)
Product Specification 5054320000-005 (PDF)	RoHS Certificate of Compliance (PDF)
Product Specification 5054321000-PS-002 (PDF)	

Agency Certification

UL E29179

General

Product Family	PCB Headers
Series	505433
Application	Signal, Wire-to-Board
Component Type	PCB Header
Overview	Micro-Lock Plus Connector System
Product Name	Micro-Lock Plus
Taxonomy	PCB Headers and Receptacles
UPC	889056765275

Physical

Breakaway	No
Circuits (Loaded)	10
Circuits (maximum)	10
Color - Resin	Black
Durability (mating cycles max)	30
First Mate / Last Break	No
Glow-Wire Capable	No
Guide to Mating Part	No
Keying to Mating Part	None
Lock to Mating Part	Yes
Material - Metal	Brass
Material - Plating Mating	Tin-Bismuth
Material - Plating Termination	Tin-Bismuth
Material - Resin	Polyamide
Net Weight	671.650/mg
Number of Rows	2
Orientation	Vertical
PCB Locator	No
PCB Retention	Yes
Packaging Type	Embossed Tape on Reel
Pitch - Mating Interface	1.25mm
Pitch - Termination Interface	1.25mm
Plating min - Mating	1.000µm
Polarized to Mating Part	Yes
Polarized to PCB	Yes
Robotic Placement	Vacuum Pick-Up Tape
Stackable	No
Temperature Range - Operating	-40° to +105°C



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

Compliant

REACH SVHC

Not Contained per -
D(2022)9120-DC (17
Jan 2023)

Halogen-Free

Status

Not Low-Halogen

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

China RoHS

Green Image

Not Relevant

Not Contained

Search Parts in this Series

[505433 Series](#)

Mates With

[Micro-Lock Plus Receptacle Housing](#)
[505432](#)

Termination Interface: Style

Surface Mount

Electrical

Current - Maximum per Contact

1.5A

Voltage - Maximum

50V AC (RMS)/DC

Material Info

Reference - Drawing Numbers

Application Specification

5054320000-AS-000, AS-505432-001-001

Packaging Specification

5054339200-200

Product Specification

2145270000-PS-000, 5054320000-002,
5054320000-005, 5054321000-PS-002, 5054321000-
PS-006

Sales Drawing

5054330000-000

This document was generated on 03/16/2023

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION