
## EAO – Your Expert Partner for **Human Machine Interfaces**

### 52-271.022 - Selector switch 2 positions

#### 52-271.022 - Selector switch 2 positions



Attention: The preview is based on a sample product. This can differ from your current configuration.

Mounting

Mounting cut-out Ø 16 mm Design raised

Front

Front dimension Ø 18 mm Front shape round

**Other Attributes** 

Weight 0,006 kg

Operating-/Indication part

Switching angle 90° right

Lever illumination

Lever shape short Lever material Plastic

**IP-Rating** 

Front protection IP65

**Connection Method** 

Terminal Solder 2.8 x 0.5 mm

**Actuator** 

Switching action Rest - Maintain

Switching element

Rotary positions 2

Switching system Snap-action switching element

Contacts 1 NC + 1 NO

Switching current 5 A


Contact material gold-plated silver Switching voltage 250 V AC

eao 🔳

# EAO – Your Expert Partner for **Human Machine Interfaces**


## 52-271.022 - Selector switch 2 positions

#### **Dimensions**




H = Universal terminal 2.0 x 0.5 mm


#### **Mounting cut-outs**



#### Wiring diagram



#### **Switching positions**



#### **Additional information**

illuminative

#### Legend

Contacts: NC = Normally closed, NO = Normally open Switching action: A = Rest, C = Maintained