

# Eaton E50AL1P5

Catalog Number: E50AL1P5

Eaton E50 NEMA heavy duty plug-in limit switch,5 Pin Mini Connector,10A at 240Vac,1A at 125Vdc,1NO-1NC,Die Cast Zinc,NEMA 1,3,3S,4,4X,6,6P,13,IP67,10A,1A,10° to 201°F (-12° to 94°C),Side Rotary

## General specifications

Product Name	Catalog Number
Eaton E50 NEMA heavy duty plug-in limit switch	E50AL1P5
	UPC
	782113645957
Product Length/Depth	Product Height
1.54 in	4.22 in
Product Width	Product Weight
2.46 in	1.275 lb
Warranty	Compliances
1 year	CE Marked
Certifications	Catalog Notes
CSA Certified UL Listed	CW (clockwise) and CCW (counterclockwise) operation; easily convertible to CW only or CCW only operation



## Product specifications

### Enclosure material

Die cast zinc

### Contact configuration

1 NO-1 NC

### Accuracy

Refer to installation publication P15836

### Switch type

Side rotary

### Contact Rating

10A at 240Vac, 1A at 125Vdc

### Operating temperature - min

10 °F

### Maximum AC current

10 A

### Maximum DC current

1 A

### Operating temperature - max

201 °F

### Connection

5-pin mini connector

### Environmental rating

NEMA 1, NEMA 3, NEMA 3S, NEMA 4, NEMA 4X, NEMA 6,  
NEMA 6P, NEMA 13, IP67

## Resources

### Catalogs

[Eaton's Volume 8—Sensing Solutions](#)

### Specifications and datasheets

[Eaton Specification Sheet - E50AL1P5](#)



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com  
© 2023 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)