

NL-350R | RECHARGEABLE NECK LIGHT

- High quality 350 lumen 6500k white SMD LEDs
- Super lightweight, adjustable and comfortable
- 2 light heads can be adjusted independently
- Super tough polycarbonate & ABS construction
- Up to 120° wider lighting angle
- IK07 Shock proof 2m drop resistant
- IP54 Dust & water resistant
- Circuit protection prevents battery from overcharging or over-discharging
- **BATTERY** 3.7v 700mAh Li-ion

WEIGHT 140g

DIMENSIONS 230 x 150 x 23mm

- High quality 3.7v 700mAh Li-ion battery
- 3 colour LED battery level indicator
- Charging indicator Green flash: Charging / Green: Fully Charged
- Low battery power warning
- USB-C charging cable included quick 2½ hour charge time

LUMEN 350LM | RUNTIME 2-10H | BEAM 45M | IP RATING IP54/IK07

WWW.UNILITE.CO.UK #BUILT TOUGH