



## VarioPlate Insert Grommet Small Single 4-5 mm

Art.-No. 440-00006 | VP-S\_4-5\_Ins-sgl-PL-BK | [Details](#)



- Integrated cable diameter tolerance compensation
- Modular application for both insert sizes (S and L)
- Integrated strain relief
- IP 65 and IP 66



More products in this product group:

[VarioPlate Cable Entry System >](#)

## Base Data


---

Application	VarioPlate cable entry system inserts grommets are used in combination with VarioPlate frames for time and space saving cable installation on all types of panel builder housings and controll boxes. The versatile design covers cable diameter from 3 to 33mm. Inserts grommets are available in one, two, four holes and blindplugs.
Application Tool	<a href="#">VP Mounting Tool</a>
Cable $\varnothing$ max	5.0 mm
Cable $\varnothing$ min	4.0 mm
Colour	Black (BK)
Description	VarioPlate Insert Grommet Small Single 4-5 mm
Material	Plastic (PL)
Pack Content	20 pcs.
Package Content packed in	bag
PART DESCRIPTION	VP-S_4-5_Ins-sgl-PL-BK
Product Family	VarioPlate Insert Grommet Small Single 4-5 mm
Product Group	VarioPlate Cable Entry System
Variant	Both sides open

---

## Product Dimensions




---



Depth (D)	32.00 mm
Height (H)	21.8 mm
Length (L)	21.1 mm
Width (W)	21.1 mm

---

## Specifications

ELV compliant (Article 4 - 2)	YES
Flammability	UL 94 V0
Halogen-free	Yes
Hazardous good	No
IP-Rating	IP66
Operating Temperature	-40 °C to +100 °C
Self extinguishing (Yes/No)	Yes
Specifications	  
Specifications	csa-C22.2 No. 94.1, csa-C22.2 No. 94.2, UL 50, UL 50E
UL OCD link	<a href="#">Link</a> <a href="#">Link</a>
UL-File Number	E526974

---

## Logistics and Packaging

---

GTIN-13 / EAN	4031026686202
Packaging 1 - Height (m)	0.07 m
Packaging 1 - Length (m)	0.11 m
Packaging 1 - Qty	20
Packaging 1 - Type	carton
Packaging 1 - Volume (m <sup>3</sup> )	0.00081 m <sup>3</sup>
Packaging 1 - Weight (kg)	0.16 kg
Packaging 1 - Width (m)	0.105 m
Packaging 2 - Height (m)	0.216 m
Packaging 2 - Length (m)	0.3048 m
Packaging 2 - Type	carton
Packaging 2 - Volume (m <sup>3</sup> )	0.0176 m <sup>3</sup>
Packaging 2 - Width (m)	0.267 m

---

## More Information

Subscribe to our newsletter >

