Pushbutton Switch Sealed

multicomp PRO

Specifications

RoHS Compliant



Case : DAP, Rated UL94V-0
Plunger : Brass, Colour Black w/ 0-Ring
Bushing : Brass, Colour Black w/ 0-Ring
Movable Contact : Copper Alloy, Silver Plated
Terminal : Copper Alloy, Silver Plated

Electrical

Rating : 1A @ 120V AC or 38V DC

 $\begin{tabular}{ll} Contact Resistance & : $10m\Omega$ max. \\ Insulation Resistance & : $1000M\Omega$ min. \\ \end{tabular}$

Dielectric withstanding voltage : 1500V RMS @ sea level Life : 50,000 cycles at full load


Temperature Rating


Operating temperature : -30°C to +85°C

Environmental


Sealed Rated : IP68

Diagram





CIRCUIT DIAGRAM (SPDT)



Dimensions : Millimetres

Part Number Table

Description	Part Number
Pushbutton Switch, SPDT, On-MOM, PCB Tails	MP-PB10-CBB2QE-4

Important Notice: This data sheet and its contents (the "Information") belong to the members of the AVNET group of companies (the "Group") or are licensed to it. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but the Group assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information and the suitability of the products for their purpose and not make any assumptions based on information included or omitted. Liability for loss or damage resulting from any reliance on the Information or use of it (including liability resulting from negligence or where the Group was aware of the possibility of such loss or damage arising) is excluded. This will not operate to limit or restrict the Group's liability for death or personal injury resulting from its negligence. Multicomp Pro is the registered trademark of Premier Farnell Limited 2019.

Newark.com/multicomp-pro Farnell.com/multicomp-pro sg.element14.com/b/multicomp-pro

