

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [2159131002](#)
Status: **Active**
Overview: [Mini-Fit Family Power Connectors](#)
Description: Mini-Fit Max Receptacle Housing, Single Row, UL 94V-0, 2 Circuits, Glow-Wire Capable, Black

Documents:

Drawing (PDF)	Test Summary 2125150000-TS-000 (PDF)
Product Specification 2125150000-PS-000 (PDF)	Datasheet (PDF)
Packaging Specification 2125140001-PK-000 (PDF)	RoHS Certificate of Compliance (PDF)



Series image - Reference only

Agency Certification

UL E29179

General

Product Family	Crimp Housings
Series	215913
Application	Power, Wire-to-Board, Wire-to-Wire
Overview	Mini-Fit Family Power Connectors
Product Name	Mini-Fit Max
Taxonomy	Connector Housings
UPC	195842607910

Physical

Circuits (maximum)	2
Color - Resin	Black
Flammability	94V-0
Gender	Receptacle
Glow-Wire Capable	Yes
Keying to Mating Part	None
Lock to Mating Part	Yes
Material - Resin	Nylon
Net Weight	0.805/g
Number of Rows	1
Packaging Type	Bag
Panel Mount	No
Pitch - Mating Interface	4.20mm
Pitch - Termination Interface	4.20mm
Polarized to Mating Part	Yes
Temperature Range - Operating	-40° to +105°C

Material Info

Reference - Drawing Numbers

Packaging Specification	2125140001-PK-000
Product Specification	2125150000-PS-000
Sales Drawing	2159130000-SD-000
Test Summary	2125150000-TS-000

EU ELV

Not Relevant

EU RoHS

Compliant

REACH SVHC

Not Contained per -
D(2022)9120-DC (17
Jan 2023)

Halogen-Free

Status

Not Low-Halogen

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

China RoHS

Green Image

Not Relevant

Not Contained

Search Parts in this Series

[215913 Series](#)

Mates With

Mini-Fit Max Header [215915](#)

Use With

Mini-Fit Max Crimp Terminal [212515](#) . Mini-Fit Max TPA [212516](#)