

Product information

00 21 05 EV

Tool Case "Basic" E-Mobility



- Fit for EVs: most important VDE-tested tools and accessories neatly organised in a tool case
- Insulated tools and accessories for all work on EVs
- Complete basic EV equipment with pliers, open-ended spanner and ratchet set
- 29 insulated tool and 1 pair of insulating gloves
- Tool case "Basic" 00 21 05 with foam insert for 3/8" reversible ratchet set
- Colour coding in foam insert indicates places for removed sockets
- For garages and companies that service EVs / their own vehicle fleets

General	
Article No.	00 21 05 EV
EAN	4003773089025
Weight	7,500 g
Dimensions	410 x 200 mm
REACH compliant	does not contain SVHC
RoHS compliant	not applicable

Technical details	
Dimension exterior (interior) width mm	410 mm
Dimension exterior (interior) height mm	200 mm
Dimension exterior (interior) depth mm	465 mm

Content	
00 21 05 LE	1 x Tool Case "Basic" empty
26 16 200	1 x Snipe Nose Side Cutting Pliers (Stork Beak Pliers) ≙ 1000
70 06 160	1 x Diagonal Cutter ≙ 1000 v ▶◀
86 06 250	1 x Pliers Wrench pliers and a wrench in a single tool ≙ 1000 ∨ □
98 00 08	1 x Open-end wrench (8 mm) ≙ 1000 ∨ ◆
98 00 09	1 x Open-end wrench (9 mm) ≙ 1000 ∨ ◆
98 00 10	1 x Open-end wrench (10 mm) ≙ 1000 ∨ ◆
98 00 11	1 x Open-end wrench (11 mm) ≙ 1000 ∨ ◆

KNIPEX Quality – Made in Germany



Content	
98 00 12	1 x Open-end wrench (12 mm) ≙ 1000 V ♠
98 00 13	1 x Open-end wrench (13 mm) ≙1000 V ◆
98 20 35	1 x Screwdrivers for slotted screws (3,5 mm) ≙1000 V →
98 20 65	1 x Screwdrivers for slotted screws (6,5 mm) ≙ 1000 V
98 24 01	1 x Screwdriver for cross recessed screws Phillips® (PH1)
98 24 02	1 x Screwdriver for cross recessed screws Phillips® (PH2) ≜1000 V
98 24 03	1 x Screwdriver for cross recessed screws Phillips® (PH3) ≜1000 V
98 29 25	1 x KNIPEX Socket 3/8" for TX25 会1000V ®
98 29 27	1 x KNIPEX Socket 3/8" for TX27 会1000V ®
98 29 30	1 x KNIPEX Socket 3/8" for TX30 会1000V ®
98 29 40	1 x KNIPEX Socket 3/8" for TX40 会1000V ®
98 29 45	1 x KNIPEX Socket 3/8" for TX45 ≙1000 V ③
98 29 50	1 x KNIPEX Socket 3/8" for TX50 ≙1000 V ③
98 31	1 x Reversible Ratchet with driving square 3/8" ≙1000 V
98 35 125	1 x Extension Bar with internal/external square 3/8" ≙1000 V
98 35 250	1 x Extension Bar with internal/external square 3/8" ≙ 1000 V
98 37 10	1 x Hexagon Socket for hexagonal screws with internal square 3/8" (10 mm) ≙1000
98 37 11	1 x Hexagon Socket for hexagonal screws with internal square 3/8" (11 mm) ≙ 1000 V ③
98 37 12	1 x Hexagon Socket for hexagonal screws with internal square 3/8" (12 mm) ≙ 1000 V
98 37 13	1 x Hexagon Socket for hexagonal screws with internal square 3/8" (13 mm)
98 62 01	1 x Plastic Flat Nose Pliers insulating ≙ 1000 V □□□□□□□□□□□□□□□□□□□□□□□□□□□□□□□□
98 62 02	1 x Plastic Snipe Nose Pliers insulating ≙1000 V ── ⊖
98 65 41	1 x Electricians' Gloves insulated ≙1000 V

KNIPEX Quality – Made in Germany



Content	
98 66 30	1 x Self-Clamping Slip-On Cap ≙ 1000 V
98 66 40	1 x Plastic Slip-On Cap conical ≙ 1000 V
98 66 50	1 x Plastic Slip-On Cap conical ≙ 1000 V

technical change and errors excepted