

## **Product information**

## 00 21 50 E

## **Tool backpack Modular X18 Electro**



General
Article No.

- Fits you and your tools: practical and comfortable due to fully hinged front and back, removable tool board and padding for your back
- As individual as you are: Optimal flexibility due to innovative FIDLOCK® connectors and MOLLE webbing
- Fit for any challenge: with two separate inner compartments for tools, measuring instruments, notebook or tablet
- Durable fabric made of sustainable recycled synthetic fibers, splashproof and easy to clean
- Waterproof molded bottom made of impact-resistant plastic for a secure upright position when opened and closed, 6 cm high
- One MOLLE strap on the inside and four MOLLE straps on the outside for attaching any adapters, carabiners and accessories
- FIDLOCK® connections are fastened or unfastened in no time at all
- A total of 21 retaining loops and 37 pockets, some with zips
- Luggage strap for fixing to telescopic handles of tool cases
- 50 x 35 x 25 cm (H x W x D), empty weight 2.9 kg, tested load capacity up to 15 kg
- Equipped with 16 KNIPEX tools, a total of 22 brand tools, partly VDEtested according to DIN EN 60900
- Max. payload: 15 kgVolume: 18 litres

EAN	4003773089063	
Weight	6,600 g	
Dimensions	340 x 210 mm	
REACH compliant	does not contain SVHC	
RoHS compliant	not applicable	
Technical details		
Dimension exterior (interior) width mm	340 mm	
Dimension exterior (interior) height mm	210 mm	
Dimension exterior (interior) depth mm	530 mm	
Content		
00 11 01	1 x KNIPEX TwinKey® for all standard cabinets and shut-off systems	
00 21 50 LE	1 x KNIPEX Modular X18 empty	
08 26 185	1 x Needle-Nose Combination Pliers ★ 1000 V	
12 52 195	1 x KNIPEX PreciStrip16 Automatic Insulation Stripper (0,08 - 16 mm²)	
13 86 200	1 x Pliers for Electrical Installation (Ø 15 mm / 50 mm²) ≙ 1000 V □	
16 95 01 SB	1 x KNIPEX ErgoStrip® Universal Stripping Tool for right-handers (Ø 8,0 – 13,0 mm) //////////////////////////////////	
26 26 200	1 x Snipe Nose Side Cutting Pliers (Stork Beak Pliers) ≙ 1000 V	
70 06 160	1 x Diagonal Cutter ★ 1000 V ►	

00 21 50 E

## **KNIPEX** Quality – Made in Germany



Content	
74 06 180	1 x High Leverage Diagonal Cutter   ≙1000 V ▶◀
78 06 125	1 x Electronic Super Knips® VDE ≙1000 V ///// ✓
90 22 10 BK	1 x KNIPEX BiX® Cutter for plastic pipes and sealing sleeves
97 53 14	1 x Self-Adjusting Crimping Pliers for wire ferrules with lateral access (0,08 − 16 mm²)    WW □
98 20 35 SL	1 x Screwdriver (Slim) for slotted screws (3,5 mm) ≙ 1000 V ●
98 20 55 SL	1 x Screwdriver (Slim) for slotted screws (5,5 mm) ≙ 1000 V ●
98 25 01 SL	1 x Screwdriver (Slim) for cross-recessed screws Pozidriv® (PZ 1)   ≜ 1000 V
98 25 01 SLS	1 x (Slim) PlusMinus screwdriver Pozidriv® (PZ/S 1) ≙ 1000 V ♣
98 25 02 SL	1 x Screwdriver (Slim) for cross-recessed screws Pozidriv® (PZ 2)   ≙ 1000 V
98 52 SB	1 x Cable Knife ≙ 1000 V
01114	1 x Stabila Wooden folding rule type 1607, white, 2 m
101-0300	1 x Picard Locksmith's hammer (300 g)
18115	1 x Stabila Pocket Electric mini spirit level (68 mm)
2281	1 x Stabila spirit level type 70 (30 cm)
0022086	1 x Wera set of hex key wrenches (1,5 - 10 mm)

technical change and errors excepted