

Product information

08 25 185 SB

Needle-Nose Combination Pliers

DIN ISO 5746



- Powerful combination pliers with pointed jaws
- For all common installation and repair work.
- Handy use when working in confined areas thanks to slim head design and pointed jaws (anti-twist)
- Milled groove in the gripping area permits small parts such as nails, pins and bolts to be held and pulled
- The reliable and diverse combination pliers when out and about
- Easy cutting thanks to the high leverage joint
- With cutting edges for soft, medium-hard and hard wire
- Long service life and stable tips
- Cutting edges additionally induction-hardened, cutting edge hardness approx. 64 HRC
- High-grade special tool steel, forged, oil-hardened

General

Article No.	08 25 185 SB
EAN	4003773088851
Pliers	chrome-plated
Head	polished
Handles	with multi-component grips
Dimensions	185 x 85 x 23 mm
Standard	DIN ISO 5746
REACH compliant	does not contain SVHC
RoHS compliant	not applicable

Technical details

Cutting capacities medium hard wire (diameter)	Ø 3.8 mm
Cutting capacities hard wire (diameter)	Ø 3.0 mm
Cutting capacity copper cable, multiple-stranded	Ø 13.0 mm
Cutting capacity copper cable, multiple-stranded	25.0 mm ²

technical change and errors excepted