

Product information

13 71 200 ME

KNIPEX WireStripper

Metric version



- Clever stripping: large capacity range, sharply ground stripping profiles and intuitive positioning
- Innovative cutting geometry: easier cutting, especially of flat cables
- Hybrid design: as flat as needle-nose pliers, as wide as combination pliers for high stability with good accessibility
- Precisely ground stripping profiles for solid conductors from 0.75 - 6 mm² and fine-stranded conductors from 0.5 - 4 mm²
- Precise positioning of the wire thanks to location ridges
- Easy cutting of copper and aluminium cables up to Ø 15 mm (1/2")
- Wide, cross-hatched gripping surfaces for twisting wires
- Milled groove for secure holding and pulling of small work pieces such as nails
- Convex gripping surface on one side for secure gripping of flat material and gripping area for round material
- Outer edges for deburring pipes
- High-grade special tool steel, forged, multi stage oil-hardened

General

Article No.	13 71 200 ME
EAN	4003773088929
Pliers	black atramentized
Head	polished
Handles	plastic coated
Dimensions	200 x 46 x 14 mm
REACH compliant	does not contain SVHC
RoHS compliant	not applicable

technical change and errors excepted