

## **Product information**

## 97 52 67 DT

## Four-Mandrel Crimping Pliers for DT contacts



- Crimps all turned male and female contacts of the DT, DTM and DTP series
- Comprehensive capacity: from 0.35 mm<sup>2</sup> to 3.0 mm<sup>2</sup> (AWG 22-12)
- Complete: with precision-ground Go/NoGo gauges to check calibration
- Synchronous feed of the four mandrels achieves optimum crimping results with eight indentations (4/8-Indent)
- Universal positioning aid for flexible adjustment to all contact lengths
  Repetitive, high crimping quality due to ratchet mechanism (unlockable)
- Position settings for the crimp depth can be clearly read on the pliers
- Ergonomic design for low-fatigue work: optimised opening width, comfortable multicomponent grips, low manual force required due to lever transmission
- Go/NoGo gauges allow quick quality control at any time: Go gauge must fit, NoGo gauge must not fit
- Special quality chrome vanadium electric steel, oil-hardened

Article No.	97 52 67 DT
EAN	4003773088820
Dimensions	230 x 80 x 70 mm
REACH compliant	does not contain SVHC
RoHS compliant	not applicable

technical change and errors excepted