

## **MicroCon Female Connector**

## 32-pin, vertical, SMT



## **Technical Data**

Applications	PCB Connectors
Pitch	0.8 mm
Orientation	Vertical
Gender	Female
No. of Pins	32
Termination	SMT
Blindmate	Yes
Class	1
Max Operating Temperature	125 °C
Data Rate	3 Gbit/s
Air- and creepage distance	0.25 mm

Mating Cycles	500
Unmated Stacking Height	8 mm
Contact Plating	Gold plated
Packaging	Tape and reel 420 pcs

Part-No. 294028-E

## **MicroCon Female Connector**

32-pin, vertical, SMT