

MicroCon Male Connector

12-pin, vertical, SMT



Technical Data

Applications	PCB Connectors
Pitch	0.8 mm
Orientation	Vertical
Gender	Male
No. of Pins	12
Termination	SMT
Blindmate	Yes
Class	1
Max Operating Temperature	125 °C
Data Rate	3 Gbit/s
Air- and creepage distance	0.25 mm

Mating Cycles	500
Unmated Stacking Height	1 mm
Contact Plating	Gold plated
Packaging	Tape and reel 830 pcs

Part-No. 294133-E

MicroCon Male Connector

12-pin, vertical, SMT