

Part-No. 354310-E



SMC Board-to-Board Adapter

50-pin, vertical



Technical Data

Applications	PCB Connectors, ,
Pitch	1.27 mm
Orientation	Vertical
Gender	Male
No. of Pins	50
Current Rating	1.1 A
Max Operating Temperature	125 °C
Data Rate	3 Gbit/s
Air- and creepage distance	0.4 mm
Mating Cycles	500
Mated Stacking Height	26 mm

Packaging

Tray 26 pcs

Part-No. 354310-E

SMC Board-to-Board Adapter

50-pin, vertical