

Part-No. 364093-E



SMC Board-to-Board Adapter

26-pin, vertical



Technical Data

| | |
|----------------------------|-------------------|
| Applications | PCB Connectors, , |
| Pitch | 1.27 mm |
| Orientation | Vertical |
| Gender | Male |
| No. of Pins | 26 |
| Current Rating | 1.3 A |
| Max Operating Temperature | 125 °C |
| Data Rate | 3 Gbit/s |
| Air- and creepage distance | 0.4 mm |
| Mating Cycles | 500 |
| Mated Stacking Height | 38 mm |

Packaging

Tray 32 pcs

Part-No. 364093-E

SMC Board-to-Board Adapter

26-pin, vertical