

SMC Board-to-Board Adapter

12-pin, vertical



Technical Data

Applications	PCB Connectors, ,
Pitch	1.27 mm
Orientation	Vertical
Gender	Male
No. of Pins	12
Current Rating	1.6 A
Max Operating Temperature	125 °C
Data Rate	3 Gbit/s
Air- and creepage distance	0.4 mm
Mating Cycles	500
Mated Stacking Height	22 mm

Packaging Tray 90 pcs

Part-No. 364095-E

SMC Board-to-Board Adapter

12-pin, vertical