

**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**

**Part Number:** [2219602126](#)  
**Status:** **Active**  
**Overview:** [Off-the-Shelf Pre-Crimped Leads](#)  
**Description:** Pre-Crimped Lead PowerWize 6.00mm Female-to-Pigtail, Gold (Au) Plating, 600.00mm Length, 2 AWG, Black

**Documents:**

[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)  
[Datasheet \(PDF\)](#)

**General**

Product Family	Cable Assemblies
Series	<a href="#">221960</a>
Assembly Configuration	Pre-crimped Lead Only
Connector to Connector	PowerWize Crimp Terminals
Overview	<a href="#">Off-the-Shelf Pre-Crimped Leads</a>
Product Name	PowerWize
Taxonomy	Power and Signal Cable Assembl
UPC	196823230479

**Physical**

Cable Length	600.00mm
Circuits (Loaded)	1
Color - Resin	Black
Gender	Female-Pigtail
Material - Metal	Copper Alloy
Material - Plating Mating	Gold
Material - Plating Termination	Silver
Material - Resin	PBT
Net Weight	37.360/g
Packaging Type	Bag
Single Ended	Yes
Termination Interface: Style	Crimp or Compression
Wire Size AWG	2
Wire/Cable Type	UL 10198

**Electrical**

Voltage - Maximum	300V
-------------------	------

**Material Info**

**Reference - Drawing Numbers**

Sales Drawing	2219602126-000
---------------	----------------



**EU ELV**

**Not Relevant**

**EU RoHS**

**Compliant**

**REACH SVHC**

Not Reviewed

**Halogen-Free**

**Status**

**Not Reviewed**

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

**China RoHS**

Green Image

Not Relevant

Not Contained

**Search Parts in this Series**

[221960 Series](#)

**Use With**

6.00mm Receptacle Crimp Housing [211942](#), [2155116121](#)