


A-SLK4-R





Item number 24.0162-\*

Insulated flexible copper conductor, suitable for many types of screw clamp connections, e.g., rail mounted terminals.  $\emptyset$  4 mm rigid socket in insulator, made of brass, accepting spring-loaded  $\emptyset$  4 mm plugs with rigid insulating sleeve.

Technical data	
Diameter of plug system	4 mm
Rated Values	1000 V, CAT II, 32 A
Surface treatment electrical contact	Ni
Base material electrical contact	CuZn
Standard color(s) *	21 22 23 24 25 26 27 29
Optional color(s)	28
Test accessory acc. to	IEC EN 61010-031
User-Information	I 010
Approvals	CE