


# SEB2-R



Item number 65.9193-\*

Insulated, rigid, accepting spring-loaded  $\varnothing$  2 mm plugs with rigid insulating sleeve. The socket is pressed into pre-drilled panels of plastic, metal, etc. Round connecting pin  $\varnothing$  1.9 mm.

Technical data	
Diameter of plug system	2 mm
Rated Values	600 V, CAT III
Surface treatment electrical contact	Au
Base material electrical contact	CuZn
Standard color(s) *	<span style="background-color: black; color: white; padding: 2px;">21</span> <span style="background-color: red; color: white; padding: 2px;">22</span> <span style="background-color: blue; color: white; padding: 2px;">23</span> <span style="background-color: yellow; color: black; padding: 2px;">24</span> <span style="background-color: green; color: white; padding: 2px;">25</span> <span style="border: 1px solid black; padding: 2px;">29</span>
Test accessory acc. to	IEC EN 61010-2-030
Remarks	Accessories: Press-in tool MB2-S
Approvals	UR