


XDK-1033/I-2





Item number 66.9561-*

Made of brass with all-round insulation. The upper jaw is non-conductive to prevent accidental short-circuits on contact with the mouth open. The insulation in this version also allows it to be used in the measurement category CAT IV.

| Technical data | |
|--------------------------------------|---|
| Diameter of plug system | 4 mm |
| Rated Values | 1000 V, CAT III, 19 A / 600 V, CAT IV, 19 A |
| Surface treatment electrical contact | Ni |
| Base material electrical contact | CuZn |
| Standard color(s) * | 20 21 22 23 24 25 26 27 29 |
| Optional color(s) | 28 |
| Opening width | 39.5 mm |
| Test accessory acc. to | IEC EN 61010-031 |
| Approvals | UL, CE |