



LB-I2R







Item number 23.0030-*

Insulated Ø 2 mm rigid. Machined brass. Metal thread jacket on the insulation. The socket can be screw-mounted in predrilled panels. Flat connecting tab 2.8 mm x 0.8 mm.

| Technical data | |
|--------------------------------------|--|
| Diameter of plug system | 2 mm |
| Rated Values | 30 V, 10 A / 60 V, 10 A |
| Surface treatment electrical contact | Optalloy |
| Base material electrical contact | CuZn |
| Standard color(s) * | 2 <mark>0 21 22 23 24 25 26 27 28 29</mark> |
| Thread | M6x0,5 |
| Test accessory acc. to | IEC EN 61010-2-030 |
| Component parts | BI-LB-I2R; MU/M6x0,5; SP2 |
| Remarks | Accessories: Flat connecting receptacle FSH2,8x0,8 |