5748676-1 <

AMPLIMITE | AMPLIMITE Kit CST

TE Internal #: 5748676-1 D-Sub Backshells & Clamps, Cable Clamp Kit, Two-Piece RFI/EMI Shield, 9 Position, Size 1, Shielded, AMPLIMITE Kit CST View on TE.com >



Connectors > D-Shaped Connectors > D-Sub Accessories > D-Sub Backshells & Clamps



Protection & Strain Relief Accessory Type: Cable Clamp Kit

Cable Clamp Type: Two-Piece RFI/EMI Shield

Number of Positions: 9

Compatible With Connector Shell Size: 1

Shielded: Yes

Features

Product Type Features

/

Connector Seal Type	Grommet Seal
Protection & Strain Relief Accessory Type	Cable Clamp Kit
Configuration Features	
Number of Positions	9
Body Features	
Cable Clamp Material	Zinc Alloy
Grommets per Set	4
Shield Plating Finish	Bright
Shield Plating Material	Nickel over Copper
Cable Clamp Type	Two-Piece RFI/EMI Shield
Cable Exit Angle	180°
Mechanical Attachment	
Screw & Hole Thread Size	4-40
Dimensions	

D-Sub Backshells & Clamps, Cable Clamp Kit, Two-Piece RFI/EMI Shield, 9 Position, Size 1, Shielded, AMPLIMITE Kit CST



Accepts Cable Insulation Diameter Range	4.7 – 8.13 mm[.185 – .32 in]
Usage Conditions	
Operating Temperature Range	-55 – 105 °C[-67 – 221 °F]
Operation/Application	
Compatible With Connector Shell Size	1
Shielded	Yes
Packaging Features	
Packaging Quantity	1
Packaging Method	Kit
Other	
Connector Accessory Comment	All parts are packaged unassembled., Jackscrews must be purchased separately., Shielded cable clamps will not accept connector housings with clinch nuts.

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU

Compliant

EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2023 (233) Candidate List Declared Against: JAN 2023 (233) Does not contain REACH SVHC
Halogen Content	Not Low Halogen - contains Br or Cl > 900 ppm.
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides

D-Sub Backshells & Clamps, Cable Clamp Kit, Two-Piece RFI/EMI Shield, 9 Position, Size 1, Shielded, AMPLIMITE Kit CST



on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: https://echa.europa.eu/guidance-documents/guidance-on-reach

Compatible Parts



TE Part # CAT-AM7-248H3 IDC D-Sub: Plug Assembly, Wire to Wire, Signal, 2.77 mm




TE Part # CAT-AM7-248H8 IDC D-Sub: Receptacle Assembly, Wire to Wire, Signal, 2.74 mm

Also in the Series | AMPLIMITE Kit CST



Customers Also Bought



D-Sub Backshells & Clamps, Cable Clamp Kit, Two-Piece RFI/EMI Shield, 9 Position, Size 1, Shielded, AMPLIMITE Kit CST





Documents

Product Drawings DIE CAST CBL CLMP KIT,SZ 1

English

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_5748676-1_A.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_5748676-1_A.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_5748676-1_A.3d_stp.zip

English

By downloading the CAD file I accept and agree to the **Terms and Conditions** of use.

Datasheets & Catalog Pages AMPLIMITE Subminiature D Connectors - Cable Connectors

English

AMPLIMITE Cable Connectors and Shielding Hardware Kits QRG

English

Product Specifications

Product Specification

English

Product Specification

English

Product Environmental Compliance MD_5748676-1_07172018956_dmtec

English

MD_5748676-1_07172018956_dmtec

English

D-Sub Backshells & Clamps, Cable Clamp Kit, Two-Piece RFI/EMI Shield, 9 Position, Size 1, Shielded, AMPLIMITE Kit CST



Instruction Sheets Instruction Sheet (U.S.)

English