



WELDY HG 330-S

Description

The WELDY HG 330-S is a high-performance heat gun. Thanks to quick, infinitely variable temperature adjustment from 176 °F to 1,112 °F and a two-stage blower, the HG 330-S is great for professional and DIY jobs alike. Whether for paint or varnish removal, installing and shrinking plastic films, refreshing plastic parts with hot air, or defrosting pipes, the HG 330-S heat gun makes tasks that require hot air easier. Thanks to its high heating capabilities and blowing strength coupled with low weight and ergonomic design, the HG 330-S is the perfect tool for your unique applications.

The WELDY HG 330-S heat gun weighs less than 1.65 lbs. This means that even time-consuming work can be done effortlessly. As part of the WELDY heat gun family, the HG 330-S is available in a wide range of configurations for various applications, with practical accessories like tubular nozzles, glass protection nozzles, and spoon reflectors.

- Can be used for multiple functions
- Quick, infinitely variable temperature adjustment
- Integrated, two-stage blower
- High heat and blowing performance

Attribute	Unit	Value
Voltage	V~	120
Power	W	1400
Air volume	l/min	250 / 450
Temperature	°C	80 - 600
Size (L × W × H)	mm	250 × 80 × 230
Weight	kg	0.7