

Product data sheet

Characteristics

1.5S43F

Low voltage transformer, encapsulated buck boost, 1 phase, 1.5kVA, 120x240V primary, 12/24V secondary, Type 3R



Main

Product	Buck and Boost Transformer
Enclosure Code	8A
Enclosure Type	NEMA 3R
Insulation Temperature	356 °F (180 °C)
Primary Voltage	120 x 240 V
Power Rating	1.5 kVA
Secondary Voltage	12/24 V
Temperature Rise	115 °C

Ordering and shipping details

Category	16265-BUCK & BOOST
Discount Schedule	PE2
GTIN	785901876441
Returnability	Yes
Country of origin	MX

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	9.40 in (23.876 cm)
Package 1 Width	11.00 in (27.94 cm)
Package 1 Length	12.40 in (31.496 cm)
Package 1 Weight	37.55 lb(US) (17.032 kg)

Offer Sustainability

Sustainable offer status	Green Premium product
California proposition 65	WARNING: This product can expose you to chemicals including: Phenyl glycidyl ether, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov
REACH Regulation	REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Compliant EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
China RoHS Regulation	China RoHS Declaration
RoHS exemption information	Yes
Environmental Disclosure	Product Environmental Profile
PVC free	Yes

Contractual warranty

Warranty	18 months
----------	-----------