

XVBL8B4

Illuminated beacon, Harmony XVB, plastic, red, 70mm, flashing, integral flash discharge tube, 10 joule, 24V AC DC



Main

Range of Product	Harmony XVB Universal
Product or Component Type	Complete beacon
Beacon or indicator bank unit type	Base unit direct or tube fixing Illuminated unit
Signalling type	Flashing
Mounting diameter	2.76 in (70 mm)
Component name	XVBL
Material	Glass reinforced polyamide base unit Polycarbonate illuminated unit
Light source	Integral flash discharge tube, red
Bulb type	Flash discharge tube
[Us] rated supply voltage	24 V AC/DC

Complementary

Connections - terminals	Screw clamp terminals, <= 1 x 1.5 mm ² with cable end
[Ui] rated insulation voltage	250 V IEC 60947-1
Nominal voltage limit	0.85...1.1 Un IEC 60947-5-1
Current consumption	< 1300 mA AC < 850 mA DC
[Uimp] rated impulse withstand voltage	4 kV IEC 60947-1
Flash energy	10 J
Flashing frequency	1 Hz
CAD overall width	2.76 in (70 mm)
CAD overall height	9.13 in (232 mm)
CAD overall depth	2.76 in (70 mm)
Terminals description ISO n°1	(GND)GROUND (COM-1)PW
Net Weight	0.99 lb(US) (0.45 kg)

Environment

Product Certifications	CCC EAC CSA C22-2 No 14 UL 508
Standards	EN/IEC 60947-5-1
Protective treatment	TC
Ambient Air Temperature for Storage	-40...158 °F (-40...70 °C)
Electrical shock protection class	Class I on support tube IEC 61140 Class II on base unit IEC 61140
IP degree of protection	IP65 on fixing base XVBZ0. IEC 60529 IP66 on base unit IEC 60529
NEMA degree of protection	Type 4X UL indoor)

Ordering and shipping details

Category	22611-XVB-STACKLIGHTS
Discount Schedule	XV
GTIN	3389110844733
Returnability	No
Country of origin	CZ

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	9.96 in (25.3 cm)
Package 1 Width	3.54 in (9.0 cm)
Package 1 Length	3.54 in (9.0 cm)
Package 1 Weight	16.37 oz (464.0 g)
Unit Type of Package 2	S03
Number of Units in Package 2	12
Package 2 Height	11.81 in (30.0 cm)
Package 2 Width	11.81 in (30.0 cm)
Package 2 Length	15.75 in (40.0 cm)
Package 2 Weight	13.17 lb(US) (5.976 kg)

Offer Sustainability


Sustainable offer status	Green Premium product
California proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov
REACH Regulation	REACH Declaration
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
Mercury free	Yes
China RoHS Regulation	China RoHS Declaration
RoHS exemption information	Yes
Environmental Disclosure	Product Environmental Profile
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.

Contractual warranty

Warranty	18 months
----------	-----------

Illuminated Beacon with “Flash” Discharge Tube Unit

Dimensions



Illuminated Beacon

Wiring Diagram

