



26081906

Polyester Ex Enclosure Ex empty

75 x 190 x 56 mm

Polyester Ex Enclosure Ex empty 75 x 190 x 56 mm

[Catalogues](#)
[Operating manuals](#)
[Declaration of Conformity](#)
[Drawing](#)
[3D Data](#)

Technical data

Height	75 mm
Width	190 mm
Depth	56 mm
Material	Polyester
Colour	Graphite black (RAL 9011)
Ingress protection	IP66
Degree of protection norm	EN 60529
temperature min.	-55 °C
temperature max.	135 °C
Seal material	VMQ-(silicone)
Flammability enclosure (certification)	UL 94 V-0
Toxicity	Halogen free
Surface resistance	10^9 Ohm
Surface resistance norm	IEC 60093
Other versions on request	EMV
Special colours on request	No
Approvals	ABS, ATEX, CCOE India, EAC (TR CU), EXPLOLABS, IECEX, INMETRO, ISCVE Ukraine, UL Ex

Commercial data

Country of origin	DE
Order unit	1 Piece
Customs tariff number	39269097
Weight	0.515 kg
GTIN	4250157916211

ETIM classification

ETIM 8	EC002503
--------	----------

Accessories



10011107

Mounting plate for 02.081906



10061010

DIN rail 15 for 01.061903