



27020400

Beluga 220, open

Beluga 220, open

[Catalogues](#)[Assembly instructions](#)[Declaration of Conformity](#)[Drawing](#)[3D Data](#)

Technical data

Height	220 mm
--------	--------

Width	116 mm
-------	--------

Depth	51 mm
-------	-------

Material	Polyamide 6 (PA6)
----------	-------------------

Colour	black-grey (RAL 7021)
--------	-----------------------

Ingress protection	IP65
--------------------	------

Degree of protection norm	EN 60529
---------------------------	----------

temperature min.	-40 °C
------------------	--------

temperature max.	60 °C
------------------	-------

Seal material	CR-(Chloroprene)
---------------	------------------

Surface resistance	10 ¹² Ohm
--------------------	----------------------

Other versions on request	EMV
---------------------------	-----

Commercial data

Country of origin	HU
Order unit	1 Piece
Customs tariff number	39269097
Weight	0.247 kg
GTIN	4250157916983

ETIM classification

ETIM 8	EC001031
--------	----------

ROSE SYSTEMTECHNIK GMBH
Erbeweg 13-15
32457 Porta Westfalica, Germany

Tel.: +49 571 50 41-0
Fax: +49 571 50 41-6
Mail: rose@rose-pw.de

Accessories

	27020080 Beluga 180/220 Hook set without magnet		27020081 Beluga 180/220 Hook set with magnet
	27020082 Beluga 180/220 Screw set		27020085 Beluga 180/230 Battery box
	27020086 Beluga Holder for Battery box (4 Mignon		27020087 Beluga Holder for Battery box (9V Block
	27020483 Beluga 220 Replacement Display screen set		82100005 MEMBRANE KEYPADS printed
	82100006 MEMBRAN KEYPADS w.subtrack		