



Order symbol: AR1083CHFL
Product nbr: 8561638
Description: PC Enclosure
Remarks: Hinged opaque flat cover w/Plastic quick release latch.

EAN: 6418074098115
El. number:
Finland:

Including: Hinged cover. Base with 10-32 brass inserts, latched flat cover with formed in place PUR gasket, and stainless hinge pin. Quick release latches. (Latch options available.). Enclosure mounting foot kit. Accessory 10-32 screws for panel mounting.

Sample photo

Dimensions:				Accessories:	
mm:	254	203	76	ALBP108	Aluminum Back Panel
inch:	10.0	8.0	3.0	ADFP108	Dead Front Panel w/ screws
				ASP108	Aluminum Swing Panel
				ASPK108	Swing Panel Kit incl. Panel
				ASPHK10	Swing Panel Kit w/o Panel
				AMFL8	8" Mounting Flange Set
Materials:				Rating:	
Material:	Polycarbonate			Ingress Protection (EN 60529): IP66/IP67	
Base colour:	RAL 7035 -light grey			Impact Resistance (EN 62262): IK09	
Cover screws material:	Stainless steel			Electrical insulation: Totally insulated	
Cover colour:	RAL 7035 -light grey			Halogen free (DIN/VDE 0472, Part 815): 1	
Gasket material:	Polyurethane			UV resistance: UL 508	
				Flammability Rating: UL 508	
				Glow Wire Test (IEC 695-2-1) °C: 960	
				NEMA Class: NEMA 4, 4X, 6, 6P, 12, 13	
Temperatures:				Certificates:	
Temperature °C (short term):	-40 ... 140 °C			Gost R	
Temperature °C (continuous):	-40 ... 80 °C				
Temperature °F (short term):	-40 ... 284 °F				
Temperature °F (continuous):	-40 ... 175 °F				
Accessories:					
ABP108	Painted Steel Back Panel				

