

AR14126CHFL



Sample image

Order symbol : AR14126CHFL

Product nr : 8561692

Description : PC Enclosure

Remarks : Hinged opaque flat cover w/Plastic quick release latch.

EAN : 6418074098658

Including : Hinged cover. Base with 10-32 brass inserts, latched flat cover with formed in place PUR gasket, and stainless hinge pin. Quick release latches. (Latch options available.). Enclosure mounting foot kit. Accessory 10-32 screws for panel mounting.

Dimensions :	Height	Width	Depth
mm :	356	305	152
inch :	14	12	6

Materials :

Material :	Polycarbonate
Base colour :	RAL 7035 -light grey
Cover colour :	RAL 7035 -light grey
Gasket material :	Polyurethane

Temperatures :

Temperature °C (short term) :	-40 ... 140
Temperature °C (continuous) :	-40 ... 80
Temperature °F (short term) :	-40 ... 250
Temperature °F (continuous) :	-40 ... 175

Accessories :

ABP1412	Painted Steel Back Panel
ASP1412	Aluminum Swing Panel
ASPHK14	Swing Panel Kit w/o Panel
AMFL12	12" Mounting Flange Set
ADFP1412	Dead Front Panel w/ screws
ALBP1412	Aluminum Back Panel
APBP1412	PVC Back Panel
ASPK1412	Swing Panel Kit incl. Panel

Ratings :

Ingress protection (EN 60529):	IP66; IP67;
Impact Resistance (EN 62262):	IK09;
electrical_insulation :	Totally insulated
Halogen free (DIN/VDE 0472, Part 815) :	Yes
UV resistance :	UL 508
Flammability Rating :	UL 508
Glow Wire Test (IEC 695-2-1) °C :	960 °C
NEMA Class	NEMA 4, 4X, 12 and 13