

Order Symbol: AR IPW 1816 SC

Description: Instrument Protection Window

Remarks : Gray Screw Cover

Includes: Cover and base with formed in place PUR gasket and hardware and template for mounting frame.



SAMPLE IMAGE

Product Number 8561846

Dimensions	Length	Width	Height
Inch	18.0	16.0	3.31
mm	457.2	406.4	84.1

Materials	
Material:	Polycarbonate
Base Color:	RAL 7035 - LIGHT GREY
Cover Color:	RAL 7035 - LIGHT GREY
Gasket material:	Polyurethane

Temperature	
Temperature C° (short term):	-40° - 120° C"
Temperature C° (continuous):	-40° - 80° C"
Temperature F° (short term):	-40° - 250° F
Temperature F° (continuous):	-40° - 175° F

Ratings	
NEMA Class	NEMA 4, 4X, 12, & 13
Ingress Protection (EN 60529):	IP66
Impact Resistance (EN 62262):	IK 09
Electrical insulation:	Fully Insulated
Halogen free (DIN/VDE 0472, Part 815):	YES
UV Resistance:	UL 508
Flammability Rating:	UL94-5VA (f1)
Glow Wire Test (IEC 695-2-1) °C:	960 °CC