### **Ap1300 SERIES**



## COMPACT PORTABLE PRINTER

With Bluetooth® option



## Unique SINGLE-handed easy paper-load system

No other printer is easier!

#### Typical applications include:

Healthcare Retail Leisure Hospitality Data Logging Warehouse Automation & Distribution POS

#### Design registered

## COMPACT AND STYLISH

- Bluetooth<sup>®</sup> compatible for flexible use with all smart phones and tablets for a truly connected business
- Wearable, portable hands free for accelerated productivity
- Utilising a high speed and high quality fixed head thermal mechanism with superb quality text and graphics
- Thermal printing requires no ink for more cost effective printing
- Intelligent battery management for optimal efficiency
- Battery life capacity of up to 4 full paper rolls to reduce down time



#### Head Office


Design, Sales, Technical Support and Repairs

Able Systems Limited Denton Drive Northwich Cheshire CW9 7TU England

**Tel:** +44 (0) 1606 48621 **Fax:** +44 (0) 1606 44903

Visit: www.able-systems.com







# **COMPACT PORTABLE PRINTER**

......

With **Bluetooth®** option

| Specification                 | Ap1300   | Ap1300BT   |  |  |  |  |
|-------------------------------|--|--|--|--|--|--|
| Data Input                    | RS-232 Serial<br>(RJ12 connector)  | RS-232 Serial<br>(RJ12 connector)  |  |  |  |  |
| Wireless Data Input           | N/A  | Bluetooth <sup>®</sup> V2.1 (Profiles: LM, L2CAP, RFCOMM, SDP, TCS, SSP and IAP. OPP optional) |  |  |  |  |
| Print Method                  | Fixed head thermal mechanism   |  |  |  |  |  |
| Print Speed                   | 60 mm/s (at 7.2V battery voltage); 50mm/s (typical)  |  |  |  |  |  |
| Paper Specification           | Paper Roll Width: 57.0 ± 0.5mm. Max roll diameter: 36mm (Length: 14.5m -16 meters).<br>Accepts paper rolls with or without a core. Paper roll A05836TPRI.  |  |  |  |  |  |
| Print Width                   | 48 mm  |  |  |  |  |  |
| Dots Per Line (Graphics)      | 384  |  |  |  |  |  |
| Dot Spacing                   | 8 dots/mm (vertical and horizontal)  |  |  |  |  |  |
| Sensors                       | Paper Out (Opto reflective) and Head Up (Mechanical)   |  |  |  |  |  |
| Data Buffer                   | 20 Kb  |  |  |  |  |  |
| Baud Rate                     | Up to 57,600 (9600 Default)  |  |  |  |  |  |
| Character Set                 | CP1252 and CP437 supplied as standard. Range of popular Code Pages available with up to 6 resident simultaneously (See note 1)   |  |  |  |  |  |
| Number Of Columns             | 12, 16, 21, 24, 42, 32 (Default). (See note 1)   |  |  |  |  |  |
| Font (Dots)                   | 7 x 24, 10 x 24 (Default). (See note 1)  |  |  |  |  |  |
| Dimensions                    | 47 x 92 x 108 mm (H x W x L)   |  |  |  |  |  |
| Weight                        | 330g (including battery and full roll of paper)  |  |  |  |  |  |
| Power Supply Options          | As standard the Ap1300 range is supplied with a shrink-wrapped re-chargeable battery pack (5 cell 6V NiMH), together with<br>an adapter to allow the use of primary cells. Note that chargers and data or power cables need to be ordered separately (see<br>below) or as part of a complete kit. Power supply options include:<br>• BC1300: Universal i/p trickle charger<br>• BC1300CLAHL: 12V/24V vehicle trickle charger |  |  |  |  |  |
| Accessories                   | <ul> <li>Ap1300BR01: Combined wall mounting bracket and belt clip</li> <li>Ap1300D9: D9 to RJ12 data cable (with jack socket for alternative charging)</li> <li>Ap1300BP01: Spare NiMH battery pack</li> </ul>   |  |  |  |  |  |
| Connectivity                  | Drivers available for Windows & Linux. Android & IOS demo apps and SDK also available. Download from www.able-systems.com  |  |  |  |  |  |
| Temperature Range (Operating) | 0 - 50°C   |  |  |  |  |  |
| Reliability - MCBF            | 10 <sup>8</sup> print pulses or 50kms. >13 million print lines (Approx. 3,500 paper rolls)   |  |  |  |  |  |

Note 1: The proprietary Font Editor Utility software (order code Ap800FEU) enables customisation of character fonts by the user.

#### **Kits**

All items available individually or as part of the below kits:

|              | Ap1300<br>Printer | Ap1300BT<br>Printer |          |          | Belt Clip /<br>Mounting Bracket | 2 Paper<br>Rolls | Primary<br>Cell Cradle | Bluetooth® |
|--------------|-------------------|---------------------|----------|----------|---------------------------------|------------------|------------------------|------------|
| Ap1300KIT1   | <b>v</b>          |                     | v        | <b>v</b> | v                               | v                | v                      |            |
| Ap1300BTKIT1 |                   | <b>v</b>            | <u>۷</u> | <b>v</b> | <ul> <li></li> </ul>            | v                | <b>v</b>               | <b>v</b>   |