

COMPACT PORTABLE PRINTER

With extra paper/label roll capacity



Unique SINGLE-handed easy paper-load system

No other printer is easier!

Typical applications include:

POS
Healthcare
Retail
Leisure Hospitality
Data Logging
In-vehicle

POWERFUL YET COMPACT

- 38 meters of print per paper/label roll reducing paper changes and minimising maintenance for operational efficiencies
- Bluetooth® compatible for flexible use with all smart phones and tablets for a truly connected business
- Utilising a high speed and high quality fixed head thermal mechanism with superb quality text and graphics
- · Linerless labels save precious time & reduce waste
- Intelligent battery management for optimal efficiency
- Robust yet compact design with the flexibility for both portable printing and wall mounting



Head Office

(Design, Sales, Technical Support and Repairs)

Able Systems Limited Denton Drive Northwich Cheshire CW9 7TU England

Tel: +44 (0) 1606 48621 **Fax:** +44 (0) 1606 44903

Visit:

www.able-systems.com



COMPACT PORTABLE PRINTER

With extra paper/label roll capacity

Specification	Ap1310	Ap1310BT				
Data Input	RS-232 Serial (RJ12 connector)	RS-232 Serial (RJ12 connector)				
Wireless Data Input	N/A	Bluetooth V2.1 (Profiles: LM, L2CAP, RFCOMM, SDP, TCS, SSP and IAP. OPP optional)				
Print Method	Fujitsu fixed head thermal mechanism					
Print Speed	60 mm/s (at 7.2V battery voltage); 50mm/s (typical)					
Paper Specification	Paper Roll Width: 57.0 ± 0.5 mm. Max roll diameter: 55 mm (typical length 37.7 m). Paper roll A05856TPR1					
Print Width	48 mm					
Dots Per Line (Graphics)	384					
Dot Spacing	8 dots/mm (vertical and horizontal)					
Sensors	Paper Out (Opto reflective) and Head Up (Mechanical)					
Data Buffer	20 Kb					
Baud Rate	Up to 57,600 (9600 Default)					
Character Set	CP1252 and CP437 supplied as standard. Range of popular Code Pages available with up to 6 resident simultaneously (See note 1)					
Number Of Columns	12, 16, 21, 24, 42, 32 (Default). (See note 1)					
Font (Dots)	7 x 24, 10 x 24 (Default). (See note 1)					
Dimensions	65 x 95 x 128 mm (H x W x L)					
Weight	446g (including battery and full roll of paper)					
Power Supply Options	As standard the Ap1310 range is supplied with a shrink-wrapped re-chargeable battery pack (5 cell 6V NiMH), together with an adapter to allow the use of primary cells. Note that chargers and data or power cables need to be ordered separately (see below) or as part of a complete kit. Power supply options include: • BC1300: Universal i/p trickle charger • BC1300CLAHL: 12V/24V vehicle trickle charger					
Accessories	 Ap1300BR01: Combined wall mounting bracket and belt clip Ap1300D9: D9 to RJ12 data cable (with jack socket for alternative charging) Ap1300BP01: Spare NiMH battery pack 					
Connectivity	Drivers available for Windows & Linux. Android & IOS demo apps and SDK also available. Download from www.able-systems.com					
Temperature Range (Operating)	0 - 50°C					
Reliability - MCBF	10° print pulses or 50kms. >13 million print lines (Approx. 3,500 paper rolls).					

Note 1: The proprietary Font Editor Utility software (order code Ap800FEU) enables customisation of character fonts by the user.

Kits

All items available individually or as part of the below kits:

	Ap1310 Printer	Ap1310BT Printer	Universal Trickle Charger	D9 Data Cable	Belt Clip / Mounting Bracket		Primary Cell Cradle	Bluetooth
Ap1310KIT1	V		V	V	✓	V	v	
Ap1310BTKIT1		v	✓	✓	✓	✓	✓	V