



NOTES:


1. HOUSING SHALL BE THERMOSETTING MOLDING MATERIAL PER MIL-M-14, TYPE SDG-F, COLOR: GREEN
2. SOCKET CONTACTS SHALL BE COPPER ALLOY GOLD PLATED PER MIL-G-45204, TYPE I CLASS I, GRADE C OVER COPPER UNDERPLATE.
3. SOCKET CONTACTS SHALL CONFORM TO CLOSED ENTRY REQUIREMENTS OF MIL-C-5015.
4. ALL HARDWARE SUPPLIED UNASSEMBLED IN SEPARATE BAG WITHIN SOCKET PACKAGE.




DETAIL "A"



"RSN116825
PCD, DATE CODE" NEAR SIDE
(EXAMPLE OF MARKING
PER ORDER)



BOTTOM MOUNTING



DETAIL "B"

REVISIONS				
ZONE	REV	DESCRIPTION	DATE	APPROVED
	-	RELEASED PER ECN NO.891	12-31-86	JAC
	A	CHG NOTE 1; GREY TO GREEN PER ECN #1736	8/7/91	MC

RSN116825		WITH MOUNTING HARDWARE	
RSN116824		WITHOUT MOUNTING HARDWARE	
QTY REQD	PART NO.	DESCRIPTION	FIND NO.
PARTS LIST			
PRECISION CONNECTOR DESIGNS INC. WINCHESTER, MA. 01890			
RELAY SOCKET 6 SIZE 16 2 SIZE 20			
SIZE	CODE IDENT NO.	DRAWING NO.	
C	58982	RSN116824	
SCALE 2/1		SHEET	

UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS ARE IN INCHES TOLERANCES	
WHOLE NUMBERS :	
1 PLACE DECIMALS :	
2 PLACE DECIMALS : .01	
3 PLACE DECIMALS : .005	
4 PLACE DECIMALS :	
ANGLES :	
MATERIAL :	
NEXT ASSY	USED ON
APPLICATION	

SEE NOTES 1 & 2

INTERPRET DRAWING PER :	
DR. <i>R. Cameron</i>	12-31-86
CHK. <i>J. Candore</i>	12-31-86
APPROVED	
ENG.	
PROD. ENG.	
BY DIRECTION OF <i>W. K. Kabin</i>	