

MATERIALS AND FINISHES:

MCX PLUG R/A CONNECTOR:

BODY, CRIMP TUBE, CAP: BRASS  
PLATED NICKEL

CENTER CONTACT: BRASS  
PLATED GOLD

OUTER CONTACT: BERYLLIUM COPPER  
PLATED GOLD

INSULATOR: PTFE

MHF® I LK CONNECTOR



CABLE: 1.37MM CABLE

HEAT SHRINK TUBE: PE

PERFORMANCE REQUIREMENTS

FREQUENCY RANGE: 0~6GHz  
IMPEDANCE: 50 Ω  
WITHSTAND VOLTAGE(AC): 350V @0.5mA  
CONTINUITY: 100% TEST

PACKAGING BY PLASTIC BAG



PART # 73230-6150

FUNCTIONAL SYMBOLS	THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION										
	DIMENSION UNITS	SCALE	CURRENT REV DESC:								
$\frac{F}{A} = 0$	MM/INCH	4:1	EC NO: 721426								
$\frac{F}{C} = 0$	GENERAL TOLERANCES (UNLESS SPECIFIED)		DRWN: YHUANG11 2022/07/20								
$\frac{F}{P} = 0$	ANGULAR TOL ± °		CHK'D: MYLU07 2022/09/19								
DIVISIONAL SYMBOLS	4 PLACES ±		APPR: LCHEN03 2022/09/22								
	3 PLACES ±		INITIAL REVISION:								
	2 PLACES ±		DRWN: YHUANG11 2022/07/20								
	1 PLACE ±		APPR: LCHEN03 2022/09/22								
0 PLACES ±		DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS		THIRD ANGLE PROJECTION	DRAWING	SERIES	MATERIAL NUMBER	CUSTOMER	DOC TYPE	DOC PART	REVISION
					C-SIZE	73230	73230-6150	GENERAL MARKET	PSD	000	A

DOCUMENT STATUS	P1	RELEASE DATE	2022/09/22	07:56:03
-----------------	----	--------------	------------	----------