



02122209

Polyester Enclosure Standard

120 x 220 x 91 mm

Polyester Enclosure Standard 120 x 220 x 91 mm

[Catalogues](#)[Declaration of Conformity](#)[Drawing](#)[3D Data](#)[Assignmentplan](#)[Terminal Mounting](#)

Technical data

Height	120 mm
Width	220 mm
Depth	91 mm
Material	Polyester
Colour	Squirrel Gray (RAL 7000)
Ingress protection	IP66
Degree of protection norm	EN 60529
Impact strength	IK09
temperature min.	-40 °C
temperature max.	90 °C
Seal material	CR-(Chloroprene)
Insulation	Fully insulated according to VDE 0100
Toxicity	Halogen free
Surface resistance	>10 ¹² Ohm
Surface resistance norm	IEC 60093
Special colours on request	Yes
Approvals	Lloyd Register, Maritime Register, UL 508A

Commercial data

Country of origin	IN
Order unit	1 Piece
Customs tariff number	39269097
Weight	1.082 kg
GTIN	4250157900654

ETIM classification

ETIM 8	EC000058
--------	----------

ROSE SYSTEMTECHNIK GMBH
Erbeweg 13-15
32457 Porta Westfalica, Germany

Tel.: +49 571 50 41-0
Fax: +49 571 50 41-6
Mail: rose@rose-pw.de

Accessories



10011008

Mounting plate for 01.122208



10027001

HINGE EXTERNAL / GREY



10061422

DIN rail 35/7,5 for xx.122208



10062002

Earth rail for 01.122208