



04202007

Aluminium Enclosure Aluform

200 x 200 x 72 mm

Aluminium Enclosure Aluform 200 x 200 x 72 mm

[Catalogues](#)[Assembly instructions](#)[Declaration of Conformity](#)[Drawing](#)[3D Data](#)[Assignmentplan](#)[Terminal Mounting](#)

Technical data

Height	200 mm
Width	200 mm
Depth	72 mm
Material	Aluminium
Material quality	DIN EN 1706 EN AC-AISI 12 (Fe)
Colour	Agate grey (RAL 7038)
Ingress protection	IP66
Degree of protection norm	EN 60529
Impact strength	IK09
temperature min.	-60 °C
temperature max.	130 °C
Seal material	PU (polyurethane) (standard)
Flame spread, sideways	HL 3
Rate of head dispersion	HL 3
Other versions on request	EMV, SBG, SWB, SBGL
Special colours on request	Yes
Approvals	Lloyd Register, Maritime Register, UL 508A

Commercial data

Country of origin	IN
Order unit	1 Piece
Customs tariff number	85369095
Weight	1.3 kg
GTIN	4250157901200

ETIM classification

ETIM 8	EC000058
--------	----------

ROSE SYSTEMTECHNIK GMBH
Erbeweg 13-15
32457 Porta Westfalica, Germany

Tel.: +49 571 50 41-0
Fax: +49 571 50 41-6
Mail: rose@rose-pw.de

Accessories

**04000010**

Aluform External hinges

**04000020**

Aluform Lid safety strip

**04000200**

Aluform External mounting bracket 200

**10011037**

Mounting plate for 04.202007

**10061009**

DIN rail 15 for 01.102008

**10061473**

DIN rail 35/7,5 for 04.102006