



27020201

Beluga 180, closed

Beluga 180, closed

[Catalogues](#)[Assembly instructions](#)[Declaration of Conformity](#)[Drawing](#)[3D Data](#)

Technical data

Height	187 mm
Width	106 mm
Depth	50 mm
Material	Polyamide 6 (PA6)
Colour	black-grey (RAL 7021)
Ingress protection	IP65
Degree of protection norm	EN 60529
temperature min.	-40 °C
temperature max.	60 °C
Seal material	CR-(Chloroprene)
Surface resistance	10 ¹² Ohm
Other versions on request	EMV

Commercial data

Country of origin	HU
Order unit	1 Piece
Customs tariff number	39269097
Weight	0.228 kg
GTIN	4250157916976

ETIM classification

ETIM 8	EC001031
--------	----------

ROSE SYSTEMTECHNIK GMBH
Erbeweg 13-15
32457 Porta Westfalica, Germany

Tel.: +49 571 50 41-0
Fax: +49 571 50 41-6
Mail: rose@rose-pw.de

Accessories

	27020080 Beluga 180/220 Hook set without magnet		27020081 Beluga 180/220 Hook set with magnet
	27020082 Beluga 180/220 Screw set		27020085 Beluga 180/230 Battery box
	27020086 Beluga Holder for Battery box (4 Mignon		27020087 Beluga Holder for Battery box (9V Block