

04161608

## Aluminium Enclosure Aluform

160 x 160 x 81 mm

Aluminium Enclosure Aluform 160 x 160 x 81 mm

[Catalogues](#)
[Assembly instructions](#)
[Declaration of Conformity](#)
[Drawing](#)
[3D Data](#)
[Assignmentplan](#)
[Terminal Mounting](#)

## Technical data

Height	160 mm
Width	160 mm
Depth	81 mm
Material	Aluminium
Material quality	DIN EN 1706 EN AC-AISI 12 (Fe)
Colour	Agate grey (RAL 7038)
Ingress protection	IP66
Degree of protection norm	EN 60529
Impact strength	IK09
temperature min.	-60 °C
temperature max.	130 °C
Seal material	PU (polyurethane) (standard)
Flame spread, sideways	HL 3
Rate of head dispersion	HL 3
Other versions on request	EMV, SBG, SWB, SBGL
Special colours on request	Yes
Approvals	Lloyd Register, Maritime Register, UL 508A

## Commercial data

Country of origin	IN
Order unit	1 Piece
Customs tariff number	85369095
Weight	1.12 kg
GTIN	4250157901170







## ETIM classification

ETIM 8	EC000058
--------	----------

ROSE SYSTEMTECHNIK GMBH  
Erbeweg 13-15  
32457 Porta Westfalica, Germany

Tel.: +49 571 50 41-0  
Fax: +49 571 50 41-6  
Mail: [rose@rose-pw.de](mailto:rose@rose-pw.de)

## Accessories

	<b>04000010</b> Aluform External hinges		<b>04000020</b> Aluform Lid safety strip
	<b>04000160</b> Aluform External mounting bracket 160		<b>10011064</b> Mounting plate for 04.161608
	<b>10061008</b> DIN rail 15 for 01.101608		<b>10061472</b> DIN rail 35/7,5 for 04.101606