

# ROLINE HDMI 10K Ultra High Speed Cable, M/M, black, 2 m

<b>Product No.</b>	11.04.5942
<b>Manufacturer</b>	ROLINE
<b>Manufacturer No.</b>	11.04.5942
<b>EAN (single piece)</b>	7630049615649



## High quality HDMI cable with resolutions up to 10K (10240 x 4320) at 30Hz!

- Supports a resolution of up to 10240x4320 pixels at a refresh rate of up to 30Hz!
- Maximum resolutions: 10K (10240x4320) @30Hz; 8K (7680x4320) @60Hz; 5K (5120x2880) @120Hz; 4K (3840x2160) @240Hz
- Dynamic HDR for particularly rich colours
- Display Stream Compression (DSC) 1.2 at particularly high resolutions on from 8K
- Variable refresh rate (VRR), to eliminate delays and jerky images
- Supports 3D video output
- Gold-plated contacts for secure data transmission

### Technical specifications

Manufacturer	ROLINE
Product group	Cable
Product type	HDMI Ultra HD with Ethernet Cable
Colour	black
Length	2 m

Transfer quality	HDMI Ultra High Speed (HDMI 2.1)
Max. resolution	10240 x 4320 @30Hz (10K, UHS)
side 1 connector	HDMI 19 Male
side 2 connector	HDMI 19 Male
Side 1 Connector Type	HDMI Type A
Side 1 Connector Gender	Male
Side 2 Connector Type	HDMI Type A
Side 2 Connector Gender	Male
Area of application	External
Cable shielding	Double screened
Weight	118.2 g
Height of packaging (single piece)	20 mm
Width of packaging (single piece)	100 mm
Depth of packaging (single piece)	100 mm
Package weight (single piece)	0.02 kg