

# ROLINE DisplayPort v1.2 Cable, TPE, DP-DP, M/M, black, 5 m

<b>Product No.</b>	11.04.5984
<b>Manufacturer</b>	ROLINE
<b>Manufacturer No.</b>	11.04.5984
<b>EAN (single piece)</b>	7630049618688



**ROLINE DisplayPort Cable with DP connection on both sides for connecting an Ultrabook, Notebook/Laptop or PC to a monitor, TV or projector - for screen transmissions in excellent quality with resolutions of up to 3840x2160 / 4096x2560 @60Hz!**

- The cable complies with the DisplayPort v1.2 standard and therefore easily reaches resolutions in the range of 4K@60Hz
- The connection requires little space and is therefore best suited for portable display devices (ultrabooks, notebooks/laptops) or for 2 connections on a graphics card (on one slot level)
- The practical plug design prevents the cable from slipping out of the DisplayPort socket
- Elastic and very flexible thanks to TPE outer sheath - best properties for cable ducts and similar applications where space is limited
- Material: TPE (Thermoplastic Elastomer)
- Compliant DP v1.2 (max. 4096 x 2560 @60Hz)

## Technical specifications

Manufacturer	ROLINE
--------------	--------

Product group	Cable
Product type	DisplayPort Monitor Cable
Colour	black
Length	5 m
Transfer quality	DisplayPort v1.2
Max. resolution	4096 x 2560 @60Hz (4K)
side 1 connector	DisplayPort M
side 2 connector	DisplayPort M
Side 1 Connector Type	DisplayPort
Side 1 Connector Gender	Male
Side 2 Connector Type	DisplayPort
Side 2 Connector Gender	Male
Area of application	External
Cable shielding	Screened
Weight	264.3 g
Height of packaging (single piece)	20 mm
Width of packaging (single piece)	200 mm
Depth of packaging (single piece)	200 mm
Package weight (single piece)	0.2 kg