
PX0599 Datasheet



Product Name // Straight Female C19 IEC Connector PX0599 Screw Terminals EN60 320-1 Standard Sheet C19 Class I

View Product Page



// Product Description:

- O Straight Female C19 IEC Connector
- O EN60 320-1 Standard Sheet C19 Class I and Standard Sheet C20 Class I
- O Cold Condition

- O Cable mount
- O Screw Terminal (rewireable)
- O Mate with PX0596, PX0598

// General Information:

Product Display Title: Product Family: Product Series: Approvals: Body Material: Current Max: Flamability Rating: Function: lec Connector Mates With: lec En60620 Type: Max Operating Temperature: Min Operating Temperature: Number Of Contacts: Voltage Max: Straight Female C19 IEC Connector IEC Connectors IEC60320 Main Inlets and Outlets CSA, ENEC, UL, VDE Nylon 66 16A, 20A UL94V-0 Straight Female Connector PX0596,PX0598 EN60 320-1 Standard Sheet C19 Class I +70°C -40°C 3 Contacts 250V

// Product PDF Links	// Product 3D CAD Model Links	// Product Certificate Links
IEC Connectors product data	PX05993D CAD Model	VDE Certificate
PX0599 IEC connector wiring		CE Certificate