

UIC558-MC-CRT-0.75-1.0 mm²/18 AWG-AG



Image is for illustration purposes only. Please refer to product description.

Part number	09 58 000 6105
Specification	UIC558-MC-CRT-0.75-1.0 mm ² /18 AWG-AG
HARTING eCatalogue	https://b2b.harting.com/09580006105

Identification

Category	Contacts
Series	HARTING UIC 558
Type of contact	Crimp contact

Version

Gender	Male
Manufacturing process	Turned contacts

Technical characteristics

Conductor cross-section	0.75 ... 1 mm ²
Conductor cross-section	AWG 18
Operating current	10 A
Contact resistance	≤4 mΩ
Stripping length	7.5 mm
Mating cycles	≥10,000

Material properties

Material (contacts)	Copper alloy
Surface (contacts)	Silver plated



Pushing Performance
Since 1945

Specifications and approvals

Specifications	UIC 50558
	IRS 50558
	IEC 61373 Category 2
	IEC 60529

Commercial data

Packaging size	50
Net weight	0.01 g
Country of origin	India
European customs tariff number	85366990
GTIN	5713140188655
eCl@ss	27440204 Contact for industrial connectors