

## UIC558-22PIN-MI-CRT



Image is for illustration purposes only. Please refer to product description.

Part number	09 58 022 3001
Specification	UIC558-22PIN-MI-CRT
HARTING eCatalogue	<a href="https://b2b.harting.com/09580223001">https://b2b.harting.com/09580223001</a>

### Identification

Category	Inserts
Series	HARTING UIC 558

### Version

Termination method	Crimp termination
Gender	Male
Number of contacts	22
PE contact	Yes
Details	Please order crimp contacts separately.

### Technical characteristics

Conductor cross-section	0.75 ... 1 mm <sup>2</sup>
Conductor cross-section	AWG 18 ... AWG 17
Rated current	10 A
Rated voltage	60 V
Insulation resistance	>10 <sup>7</sup> Ω
Limiting temperature	-50 ... +125 °C
Mating cycles	≥10,000

### Material properties

Material (insert)	Polyamide (PA)
Colour (insert)	Black



**Pushing Performance**  
Since 1945

## Material properties

Material flammability class acc. to UL 94	V-0
---	-----

## Specifications and approvals

Specifications	UIC 550
	IRS 50558
	IEC 61373 Category 2
	IEC 60529

## Commercial data

Packaging size	1
Net weight	35 g
Country of origin	India
European customs tariff number	85366990
GTIN	5713140187009
eCl@ss	27440205 Contact insert for industrial connectors