Plastic Enclosures with Door Multicomp PRO



RoHS Compliant

Features

- Available with Solid and Transparent Door Option.
- · Lockable and supplied complete with galvanized steel back plate and mounting brackets
- MP001214 and MP001222 has 1 key lock. All other sizes have 2 key locks
- Manufactured from UL Approved ABS-HB Plastic
- Meets Protection and Combustible standards IP65 & IK08
- Suitable for wide range of both indoor and outdoor applications in harsh, dry or dusty environments and also high humidity.
- Flame Retardant UL94V-HB
- Temperature range of -20°C to +85°C


Part Number Table


Description	Dimensions	Part Number
Enclosure, ABS-HB, Grey, IP65/IK08	300mm × 200mm × 130mm	MP001214
Enclosure, ABS-HB, Grey, IP65/IK08	350mm × 250mm × 150mm	MP001215
Enclosure, ABS-HB, Grey, IP65/IK08	400mm × 300mm × 170mm	MP001216
Enclosure, ABS-HB, Grey, IP65/IK08	400mm × 300mm × 220mm	MP001217
Enclosure, ABS-HB, Grey, IP65/IK08	500mm × 350mm × 190mm	MP001218
Enclosure, ABS-HB, Grey, IP65/IK08	500mm × 400mm × 240mm	MP001219
Enclosure, ABS-HB, Grey, IP65/IK08	600mm × 400mm × 200mm	MP001220
Enclosure, ABS-HB, Grey, IP65/IK08	700mm × 500mm × 250mm	MP001221
Enclosure, ABS-HB, Grey, Transparent Door, IP65/IK08	300mm × 200mm × 130mm	MP001222
Enclosure, ABS-HB, Grey, Transparent Door, IP65/IK08	350mm × 250mm × 150mm	MP001223
Enclosure, ABS-HB, Grey, Transparent Door, IP65/IK08	400mm × 300mm × 170mm	MP001224
Enclosure, ABS-HB, Grey, Transparent Door, IP65/IK08	400mm × 300mm × 220mm	MP001225
Enclosure, ABS-HB, Grey, Transparent Door, IP65/IK08	500mm × 350mm × 190mm	MP001226
Enclosure, ABS-HB, Grey, Transparent Door, IP65/IK08	500mm × 400mm × 240mm	MP001227
Enclosure, ABS-HB, Grey, Transparent Door, IP65/IK08	600mm × 400mm × 200mm	MP001228
Enclosure, ABS-HB, Grey, Transparent Door, IP65/IK08	700mm × 500mm × 250mm	MP001229


multicomp PRO

DIMENSIONS AND PRODUCT CODES

SIZE (mm)	200x300x130	250x350x150	300x400x170	300x400x220	350x500x190	400x500x240	400x600x200	500x700x250
ILLUSTRATIONS REF. CODE BELOW	MP001214 MP001222	MP001215 MP001223	MP001216 MP001224	MP001217 MP001225	MP001218 MP001226	MP001219 MP001227	MP001220 MP001228	MP001221 MP001229
Α	200	250	300	300	350	400	400	500
В	300	350	400	400	500	500	600	700
С	149	195	245	241	291	34	341	443.5
D	257	300	357	348	448	447	548	650.5
E	112	162	212	212	262	312	312	412
F	255	288	338	338	438	438	538	638
G	130	180	230	230	280	330	330	430
н	227	272	322	322	422	422	522	622
1	130	150	170	220	190	240	200	250
)	119	139	159	209	179	229	189	239
K	127	177	227	227	277	327	327	427
L	177	227	277	277	277	277	477	577
М	225	275	324.5	324.5	374.5	425	424.5	524.5
N	227	277	327	326.5	426.5	427	526.5	626.5
0	150.5	200	250	250.5	300.5	350.5	350.5	450.5
Ρ	346	391	441	441	541	541	641	741







Important Notice : This data sheet and its contents (the "Information") belong to the members of the AVNET group of companies (the "Group") or are licensed to it. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but the Group assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information and the suitability of the products for their purpose and not make any assumptions based on information included or omitted. Liability for loss or damage resulting from any reliance on the Information or use of it (including liability resulting from negligence or where the Group was aware of the possibility for such loss or damage arising) is excluded. This will not operate to limit or restrict the Group's liability for death or personal injury resulting from its negligence. Multicomp Pro is the registered trademark of Premier Famell Limited 2019.

Newark.com/multicomp-pro Farnell.com/multicomp-pro Element14.com/multicomp-pro

multicomp PRO