



HelaTape

HellermannTyton offers a comprehensive range of vinyl, rubber and cloth tapes for bundling, insulating, fixing, sealing and marking applications around all kinds of electrical applications. Vinyl electrical tapes are designed for low voltage applications and available in different dimensions and colours. Rubber tapes are suitable for sealing and insulating cables and splices in low, medium and high voltage applications. HelaTape cloth tapes are extremely strong and ideal for identification, fixing, bundling and repair purposes. HelaTape Protect is used to build professional cable and wiring harnesses.

Vinyl Electrical Tapes – Commercial Grade Vinyl Electrical Tape

HelaTape Flex 15

Features and benefits

- Vinyl electrical tape in many different colours
- Used for insulation, protection, fixing, maintenance, colour coding and more
- Good resistance to abrasion, sunlight, moisture, chemicals and varying weather conditions
- Highly flexible with outstanding adhesion performance
- Harnessing of wires and cables
- Suitable for mechanical and electrical applications up to 1 kV
- VDE approved according to IEC 60454-3-1-6/F-PVCP/90
- Flame retardant according to IEC 60454-2



HelaTape Flex 15 is a commercial grade, weather resistant vinyl tape.

MATERIAL	Polyvinylchloride (PVC)
Dielectric Strength	45 kV/mm
Adhesion to Steel	2.5 N/10 mm
Adhesion to Backing	2.5 N/10 mm
Elongation at break	200 %
Breaking Strength	28 N/10 mm
Operating Temperature	-10 °C to +90 °C



TYPE	Thickness (T)	Width (W)	Length (L)	Colour	Article-No.
HTAPE-FLEX15-15x10	0.15	15.0	10.0 m	Black (BK)	710-00104
	0.15	15.0	10.0 m	Blue (BU)	710-00100
	0.15	15.0	10.0 m	Brown (BN)	710-00107
	0.15	15.0	10.0 m	Green (GN)	710-00103
	0.15	15.0	10.0 m	Green-Yellow (GNYE)	710-00106
	0.15	15.0	10.0 m	Grey (GY)	710-00108
	0.15	15.0	10.0 m	Orange (OG)	710-00110
	0.15	15.0	10.0 m	Red (RD)	710-00101
	0.15	15.0	10.0 m	Red (RD), Grey (GY), Yellow (YE), Green (GN), Blue (BU), Orange (OG), White (WH), Brown (BN), Black (BK), Green-Yellow (GNYE)	710-00146
	0.15	15.0	10.0 m	Transparent (CL)	710-00147
	0.15	15.0	10.0 m	Violet (VT)	710-00109
	0.15	15.0	10.0 m	White (WH)	710-00105
	0.15	15.0	10.0 m	Yellow (YE)	710-00102

All dimensions in mm. Subject to technical changes.
Minimum Order Quantity (MOQ) may differ from package content.



For product specific approvals and specifications please refer to the Appendix.





Vinyl Electrical Tapes – Commercial Grade Vinyl Electrical Tape

HTape Flex 15

TYPE	Thickness (T)	Width (W)	Length (L)	Colour	Article-No.
HTAPE-FLEX15-15x25	0.15	15.0	25.0 m	Black (BK)	710-00115
HTAPE-FLEX15-19x20	0.15	19.0	20.0 m	Black (BK)	710-00155
	0.15	19.0	20.0 m	Blue (BU)	710-00151
	0.15	19.0	20.0 m	Brown (BN)	710-00158
	0.15	19.0	20.0 m	Green (GN)	710-00154
	0.15	19.0	20.0 m	Green-Yellow (GNYE)	710-00157
	0.15	19.0	20.0 m	Grey (GY)	710-00159
	0.15	19.0	20.0 m	Red (RD)	710-00152
	0.15	19.0	20.0 m	Violet (VT)	710-00160
	0.15	19.0	20.0 m	White (WH)	710-00156
0.15	19.0	20.0 m	Yellow (YE)	710-00153	
HTAPE-FLEX15-19x25	0.15	19.0	25.0 m	Black (BK)	710-00126
HTAPE-FLEX15-25x25	0.15	25.0	25.0 m	Black (BK)	710-00137
	0.15	25.0	25.0 m	Blue (BU)	710-00133
	0.15	25.0	25.0 m	Brown (BN)	710-00140
	0.15	25.0	25.0 m	Green (GN)	710-00136
	0.15	25.0	25.0 m	Green-Yellow (GNYE)	710-00139
	0.15	25.0	25.0 m	Grey (GY)	710-00141
	0.15	25.0	25.0 m	Red (RD)	710-00134
	0.15	25.0	25.0 m	White (WH)	710-00138
	0.15	25.0	25.0 m	Yellow (YE)	710-00135

All dimensions in mm. Subject to technical changes.
Minimum Order Quantity (MOQ) may differ from package content.



For product specific approvals and specifications please refer to the Appendix.



Add items to your watchlist!
www.HT.click/9-399

