

# POWER METER

## An IoT-ready HD touch screen power meter for single, split and 3 phase networks

Introducing the Vista Touch Power Meter – a cutting-edge IoT-ready high-definition touch screen power meter designed for single, split, and 3 phase networks. This revolutionary panel meter offers unparalleled power monitoring capabilities with its vibrant graphic display and intuitive touchscreen interface. Fully configurable, it supports industry-standard communication protocols such as Modbus RTU (RS485) and TCP/IP (Ethernet), as well as built-in integration with the Trumeter Cloud platform, remote monitoring is made easy right out of the box.

When you need to monitor power in a commercial or industrial setting, the Vista Touch Power Meter is the ultimate solution for precise and efficient energy management.



## FEATURES

- For single, split and 3 phase applications
- Measures Active (W) Reactive (Var) and Apparent (VA) power
- Provides clear indication of electrical circuit performance
- 1% accuracy across the input range
- Programmable Current Transformer (CT) and Potential Transformer (PT) ratios
- 2 x form C relays
- 65K color 70mm x 70mm [2.76" x 2.76"] graphics display
- Simple and intuitive touchscreen configuration
- User programmable scale and custom alarm messages
- Advanced alarm notifications
- Load and save configuration data to a USB flash drive\*
- Free access to the IoT Trumeter Cloud remote monitoring with texts and emails alarm notifications
- Modbus® RTU and TCP\*
- Industry standard ¼ DIN mounting
- Ethernet and RS485 as standard
- Modular pluggable quick connect/disconnect connectors

\*Feature available late 2023 via software update

## PART NUMBERS

VT-PWR-LV	Vista Touch Power Meter 12-24V AC/DC
VT-PWR-HV	Vista Touch Power Meter 100-277V AC