

PXMBNI16FIM03ASCPG9 Datasheet

**Product Name // M16 Series A Code Brass Nickel Plated
PG9 Inline Body 3 Contact Pins**

[View Product Page](#)



// Product Description:

- ⊕ M16 Series Brass Nickel Plated Inline Body Connectors
- ⊕ Water and dustproof to IP67 when mated with compatible connector
- ⊕ A Code
- ⊕ Pin only
- ⊕ 3, 4, 5, 6, 8, 12 Contact
- ⊕ Solder Terminals
- ⊕ Mate with M16 Series Flex Body and Panel Mount Connectors, depending on part code

// General Information:

Product Display Title:	M16 Series Brass Nickel Plated Inline Body Connectors
Product Family:	Circular Automation Connectors
Product Series:	M16 Series
Change Notes:	PRODUCT-MOQ-ADJUSTMENT
Body Material:	Brass - Nickel Plated
Contact Type:	Plug Contact
Coupling Type:	Screw
Current Max:	7A
Diameter Over Coupling Ring Mm:	18.5mm
Function:	Inline Cable Connector Body
Ip Rating:	IP67
M12 Series Mounting Nut:	PG9
Max Operating Temperature:	+80°C
Min Operating Temperature:	-25°C
Number Of Contacts:	3 Contacts
Pin Layout Code:	A Code
Thread Size:	M16 x 0.75
Voltage Max:	250V

// Product PDF Links

 [M16 Series automation connectors...](#)