


SA1024 Datasheet

Product Name // Tin Plated 15-18 AWG Stamped Plug Contact - Bandolier

[View Product Page](#)



// Product Description:

- Tin Plated 15-18 AWG Stamped Plug Contact - Bandolier
- Crimp Terminals
- Operating Temperature= -55°C to +125°C

// General Information:

<p>Product Display Title:</p> <p>Product Family:</p> <p>Product Series:</p> <p>Body Material:</p> <p>Contact Type:</p> <p>Function:</p> <p>Material Finish:</p> <p>Max Contact Accomodation Awg:</p> <p>Min Contact Accomodation Awg:</p> <p>Max Operating Temperature:</p> <p>Min Operating Temperature:</p> <p>Rohs Compliant:</p>	<p>Tin Plated 15-18 AWG Stamped Plug Contact - Bandolier</p> <p>Rectangular Connectors</p> <p>Automotive Rectangular Connectors- Contact - Bandoliers</p> <p>Cooper Alloy</p> <p>Plug Contact - Bandolier Contact - Bandolier</p> <p>Crimp Contact - Bandolier</p> <p>Tin Plated Plated</p> <p>18AWG</p> <p>15AWG</p> <p>+125°C</p> <p>-55°C</p> <p>Yes</p>
--	---

// Product PDF Links

[Rectangular Power Connector...](#)