




WLMS12 Datasheet

Product Name // 12 Contacts Socket Miniature Wedgelock

 [View Product Page](#)




// Product Description:


| | |
|--|--|
|  12 Contacts Socket Miniature Wedgelock |  Operating Temperature= -55Å°C to +125Å°C |
|--|--|


// General Information:

| | |
|----------------------------|---|
| Product Display Title: | 12 Contacts Socket Miniature Wedgelock |
| Product Family: | Rectangular Connectors |
| Product Series: | Miniature Rectangular Connectors- Wedgelocks |
| Body Colour: | Blue |
| Body Material: | Polycarbonate/Polybutylene Terephthalate (PC/PBT) |
| Contact Type: | Socket Contact |
| Function: | Wedgelock |
| Max Operating Temperature: | +125°C |
| Min Operating Temperature: | -55°C |
| Number Of Contacts: | 12 Contacts |
| Rohs Compliant: | Yes |

// Product PDF Links

 [Rectangular Power Connector...](#)

 Have a question or project enquiry you'd like to talk to us about?

 [Click Here To Contact Us](#)